Promag 10H



More information and current pricing: www.endress.com/10H

Benefits:

- Flexible installation concept numerous hygienic process connections
- Energy-saving flow measurement no pressure loss due to crosssection constriction
- Cost-effective designed for easy applications and direct integration
- Safe operation display provides easy readable process information
- Fully industry compliant IEC/EN/NAMUR
- Maintenance-free no moving parts

Specs at a glance

- Max. measurement error Volume flow: $\pm 0.5\%$ o.r. ± 2 mm/s $(\pm 0.5\% \text{ o.r.} \pm 0.08 \text{ in/s})$
- Measuring range 0.06 dm3/min to 600 m3/h (0.015 gal/min to 2650 gal/min)
- Medium temperature range $-20 \text{ to } +150 \,^{\circ}\text{C} \, (-4 \text{ to } +302 \,^{\circ}\text{F})$
- Max. process pressure PN 40, Cl. 150, JIS 20 K
- Wetted materials Liner: PFA Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022) Process Connections: stainless steel, 1.4404 (F316L); PVDF; PVC Seals: O-ring seal (EPDM, FKM, Kalrez), aseptic molded seal (EPDM, FKM, silicone)

Field of application: Promag H is the preferred sensor for applications with highest requirements in the food and beverage and life science industries. Combined with the Promag 10 transmitter for basic applications and direct integration, Promag 10H offers accurate measurement of liquids for a wide range of applications. It will be the preferred solution for customers aiming for minimized cost of ownership. Promag 10H is available in a compact or remote version.

Features and specifications

Liquids

Measuring principle

Electromagnetic

Product headline

The flowmeter for smallest flow rates with a highly cost-effective transmitter.

For demanding hygienic applications.

Sensor features

Flexible installation concept – numerous hygienic process connections. Energy-saving flow measurement – no pressure loss due to cross section constriction. Maintenance-free – no moving parts.

Liner made of PFA. Sensor housing made of stainless steel (3-A, EHEDG). Wetted materials CIP, SIP cleanable.

Transmitter features

Cost-effective – designed for easy applications and direct integration. Safe operation – display provides easily readable process information. Fully industry-compliant – IEC/EN/NAMUR.

2-line display with push buttons. Device as compact or remote version. HART.

Nominal diameter range

DN 2...150 1/12"...6"

Wetted materials

Liner: PFA

Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022) Process Connections: stainless steel, 1.4404 (F316L); PVDF; PVC Seals: O-ring seal (EPDM, FKM, Kalrez), aseptic molded seal (EPDM,

FKM, silicone)

Measured variables

Volume flow

Max. measurement error

Volume flow: $\pm 0.5\%$ o.r. ± 2 mm/s ($\pm 0.5\%$ o.r. ± 0.08 in/s)

Liquids

Measuring range

0.06 dm3/min to 600 m3/h (0.015 gal/min to 2650 gal/min)

Max. process pressure

PN 40, Cl. 150, JIS 20 K

Medium temperature range

 $-20 \text{ to } +150 ^{\circ}\text{C} (-4 \text{ to } +302 ^{\circ}\text{F})$

Ambient temperature range

 $-40 \text{ to } +60 \,^{\circ}\text{C} \, (-40 \text{ to } +140 \,^{\circ}\text{F})$

Sensor housing material

1.4301 (304), corrosion resistant

Transmitter housing material

Powder-coated die-cast aluminum

Degree of protection

IP66/67, type 4X enclosure

Transmitter remote version: IP67, type 4X enclosure

Display/Operation

2-line display with push buttons

Configuration via local display and operating tools possible

Outputs

4-20 mA HART (active)

Pulse/switch output (passive)

Inputs

None

Digital communication

HART

Liquids

Power supply

DC 11 to 40 V

AC 85 to 250 V (45 to 65 Hz)

AC 20 to 28 V (45 to 65 Hz)

Hazardous area approvals

FΜ

CSA

Product safety

CE, C-tick, EAC marking

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Pressure approvals and certificates

PED

Hygienic approvals and certificates

EHEDG, 3-A, FDA

More information www.endress.com/10H

